



	<p>Sample holder (minimum)</p> <p>System must have display</p> <p>Wedge tool length for</p> <p>Ball Bonding capillary for</p> <p>Motorized Wire feed</p>	<p>(minimum)</p> <p>2" (50 mm) x 2" (50 mm) with temperature range from ambient to 150°C.</p> <p>Bonding parameters such as bonding force, ultrasonic power, bonding time.</p> <p>50 mil gold wire 50 mil Aluminum wire</p> <p>½ Inch spool</p>	<p><b>Diagonal feed: ~19 mm</b> <b>Vertical Feed: ~15.9 mm /21 mm</b></p> <p><b>One spool (100 meter) of 1 mil Au wire</b> <b>One spool (100 meter) of 1 mill Al wire</b></p> <p><b>1 mil wire</b></p>
--	--	---	--